



M-13565

1



NOTES:

- 1. LOW VOLTAGE DEVICES: 24 VDC.
POWERED BY ROOM CONTROLLER (CAT.#LLC2RD or LLC2R,
ORDERED SEPARATELY) USING PLENUM RATED RJ45 UTP CABLE
(CAT.# UTPxxOR, ORDERED SEPARATELY).
- 2. COLOR CODED, PLUG-AND-PLAY INTEGRATION WITH ROOM CONTROLLER.
- 3. FOUR JUMPER SELECTABLE FOOT-CANDLE RANGES:
0.3-30fc; 3-300fc; 30-3,000fc; 60-6,000fc.
- 4. ALL DIMENSIONS ARE IN INCHES [mm].

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
HOUSING	THERMOPLASTIC	

DIMENSION SHEET FOR CAT. NO.
SEE TABLE

B

M-13565


1

1	NEW RELEASE PER DCN #22883	D.LI	2/7/17
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE
DAYLIGHT SENSOR, ROOM CONTROLLER

CATALOG #	DESCRIPTION	OPERATING ENVIRONMENT
RCDP	ROOM CONTROLLER DAYLIGHT SENSOR	32°F TO 104°F [0°C TO +40°C], FOR INDOOR USE.
RCODP	ROOM CONTROLLER DAYLIGHT SENSOR, OUTDOOR	-40°F TO 122°F [-40°C TO +50°C], FOR OUTDOOR USE, IP54 RATING.

 TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2'	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
	DR. BY D.LI	SCALE NONE
CHK. BY	DATE 2/7/2017	