



M-13556


1




RCSNF<sub>x</sub>  
SERIES




RCSNRLF<sub>x</sub>  
SERIES




RCSRL<sub>x</sub>  
SERIES



RCSSC<sub>x</sub>  
SERIES



RCSTO<sub>x</sub>  
SERIES



LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
BASE	THERMOPLASTIC	BLACK
COVER	THERMOPLASTIC	COLOR PER CAT.# SEE TABLE.
BUTTON	THERMOPLASTIC	COLOR PER CAT.# SEE TABLE.

- NOTES:
1. LOW VOLTAGE DEVICES: 24 VDC.  
POWERED BY ROOM CONTROLLER (CAT.#LLC2RD or LLC2R, ORDERED SEPARATELY) USING PLENUM RATED RJ45 UTP CABLE (CAT.# UTPxxOR, ORDERED SEPARATELY).
  2. FOR INDOOR USE ONLY,  
OPERATING TEMPERATURE: 32°F TO 104°F [0°C TO 40°C];  
RELATIVE HUMIDITY (NON-CONDENSING): 0 TO 95%.
  3. SWITCHES CAN BE MOUNTED TO SINGLE OR MULTI-GANG STANDARD WALL BOXES.
  4. ALL DIMENSIONS ARE IN INCHES [mm].

SWITCH TYPE	CATALOG #	DESCRIPTION	COLOR
ON/OFF	RCSNFW	ROOM CONTROLLER SWITCH, ON-OFF, WH	WHITE
ON/RAISE/LOWER/OFF	RCSNRLF	ROOM CONTROLLER SWITCH, ON-RAISE-LOWER-OFF, WH	WHITE
	RCSNRLF I	ROOM CONTROLLER SWITCH, ON-RAISE-LOWER-OFF, IV	IVORY
RAISE/LOWER	RCSRLW	ROOM CONTROLLER SWITCH, RAISE-LOWER, WH	WHITE
SCENE	RCSSCW	ROOM CONTROLLER SWITCH, SCENE, WH	WHITE
TIMED ON	RCSTOW	ROOM CONTROLLER SWITCH, TIMED ON, WH	WHITE

1	NEW RELEASE PER DCN #22883	D.LI	2/7/17
REV	DESCRIPTION	APP	DATE
<p>THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].</p>			
<p>TITLE</p> <p>ROOM CONTROLLER SPECIALTY SWITCH</p>			
<p>WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT</p>			
<p>TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2°</p>		<p>DR. BY D.LI</p> <p>CHK. BY</p>	<p>SCALE NONE</p> <p>DATE 2/7/2017</p>

DIMENSION SHEET FOR CAT. NO. **M-13556** **SEE TABLE** **B** **1**