


M-13847

1




RECEPTACLE CLOSED VIEW


LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
TOWER COVER	ALUMINUM	SEE TABLE PER CATALOG
FLANGE	ALUMINUM	SEE TABLE PER CATALOG
RECEPTACLE FACE	THERMOPLASTIC	BLACK
BOTTOM HOUSING	ALUMINUM	
MAIN BODY HOUSING	THERMOPLASTIC	
LOCK NUT	THERMOPLASTIC	
O RINGS	ELASTOMER	
WIRE CLAMP	STEEL	ZN PLATED
WIRE CLAMP SCREWS	STEEL	ZN PLATED
TERMINALS	BRASS	
CYLINDER	STEEL	
GROUND SCREWS	STEEL	ZN PLATE + GREEN
NEUTRAL SCREWS	STEEL	ZN PLATED
HOT SCREWS	STEEL	BRASS PLATE
WATER SEALS	ELASTOMER	


DIMENSION SHEET FOR CAT. NO. SEE TABLE



SURFACE MOUNT DEVICE  
CAT.# RCT220 SERIES




FLUSH MOUNT DEVICE  
CAT.# RCT221 SERIES.  
(SAME AS RCT220 SERIES  
EXCEPT FOR THE FLANGE  
WITHOUT CHAMFER  
AS SHOWN).



MOUNTING TYPE	CATALOG	DESCRIPTION	COLOR	CUT OPENING
SURFACE MOUNT SERIES	RCT220BK	20A KIT KITCHEN COUNTER TAMPER RESISTANT RECEPTACLE SURFACE MOUNT, PAINTED BLACK	BLACK	SEE FIG. 1
	RCT220W	20A KIT KITCHEN COUNTER TAMPER RESISTANT RECEPTACLE SURFACE MOUNT, PAINTED WHITE	WHITE	
	RCT220ALU	20A KIT KITCHEN COUNTER TAMPER RESISTANT RECEPTACLE SURFACE MOUNT, BRUSHED ALUMINUM	BRUSHED ALUMINUM	
	RCT220BR	20A KIT KITCHEN COUNTER TAMPER RESISTANT RECEPTACLE SURFACE MOUNT, BRUSHED BRASS	BRUSHED BRASS	
	RCT220CH	20A KIT KITCHEN COUNTER TAMPER RESISTANT RECEPTACLE SURFACE MOUNT, POLISHED CHROME	POLISHED CHROME	
	RCT220BZE	20A KIT KITCHEN COUNTER TAMPER RESISTANT RECEPTACLE SURFACE MOUNT, MATTE BRONZE	MATTE BRONZE	
	RCT220NI	20A KIT KITCHEN COUNTER TAMPER RESISTANT RECEPTACLE SURFACE MOUNT, BRUSHED NICKEL	BRUSHED NICKEL	
FLUSH MOUNT SERIES	RCT221BK	20A KIT KITCHEN COUNTER TAMPER RESISTANT RECEPTACLE FLUSH MOUNT, PAINTED BLACK	BLACK	SEE FIG. 2
	RCT221W	20A KIT KITCHEN COUNTER TAMPER RESISTANT RECEPTACLE FLUSH MOUNT, PAINTED WHITE	WHITE	
	RCT221ALU	20A KIT KITCHEN COUNTER TAMPER RESISTANT RECEPTACLE FLUSH MOUNT, BRUSHED ALUMINUM	BRUSHED ALUMINUM	
	RCT221BR	20A KIT KITCHEN COUNTER TAMPER RESISTANT RECEPTACLE FLUSH MOUNT, BRUSHED BRASS	BRUSHED BRASS	
	RCT221CH	20A KIT KITCHEN COUNTER TAMPER RESISTANT RECEPTACLE FLUSH MOUNT, POLISHED CHROME	POLISHED CHROME	
	RCT221BZE	20A KIT KITCHEN COUNTER TAMPER RESISTANT RECEPTACLE FLUSH MOUNT, MATTE BRONZE	MATTE BRONZE	
	RCT221NI	20A KIT KITCHEN COUNTER TAMPER RESISTANT RECEPTACLE FLUSH MOUNT, BRUSHED NICKEL	BRUSHED NICKEL	

NOTES:

- RECEPTACLE RATING: 20A 125V.
- TWO POWER OUTLETS AVAILABLE.
- ACCEPT NON-METALLIC SHEATHED CABLE AND/OR METAL CONDUIT (BY USING WIRE CLAMP OR 1/2" KNOCKOUT) TO WIRE THE DEVICE.
- SUITABLE FOR COUNTERTOP THICKNESS .56"-2.13" [14.3-54.0 mm].
- ALL DIMENSIONS ARE IN INCHES [mm].
- cULus LISTED.



SURFACE INSTALLATION  
FIG. 1

FLUSH INSTALLATION  
FIG. 2

1	RELEASED PER DCN#23363	EMD	3/16/18
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE  
POP UP RECEPTACLE, 20A



WIRING DEVICE-KELLEMS  
HUBBELL INCORPORATED  
SHELTON, CT

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2'	DR. BY EMD	SCALE 1/2
	CHK. BY	DATE 3/16/18

B

M-13847

1