



M-8922 4



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
HOUSING	TPE	SEE TABLE
RIVET	BRASS	
CONTACT	BRASS	
CAGE	NYLON	BLACK


CATALOG NO. HBLFRSBK
 (NOT SHOWN TO SCALE)

SYM	REVISIONS	APP	DATE
4	REVISED NOTE 2 FROM 600VAC/250VDC TO 600V PER DCN 23410 RGP	RGP	11/01/17
3	REDRAWN WITH EMBEDDED CAD MODEL WITH NO CHANGES TO PART GEOMETRY PER DCN 21895 SPN	DJP	2/5/16

HUBBELL CAT. NO.	COLOR
HBLFRSBK	BLACK
HBLFRSW	WHITE
HBLFRSGN	GREEN
HBLFRSR	RED
HBLFRSBL	BLUE
HBLFRSO	ORANGE
HBLFRSBN	BROWN
HBLFRSY	YELLOW

- NOTES:
- DIMENSIONS ARE INCHES ± .02 [mm] ± .5
 - RATING: 600V 400 AMP.
 - UL/c-UL ENCLOSURE TYPES 3R, 4X, 12, SEE INSTRUCTION SHEET

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
SINGLE POLE FEMALE RECEPTACLE W/STUD

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLES = ± 2°	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
	DR. BY MJM	APP. BY
	TR. BY	SCALE 1:1
	CHK. BY	DATE 6/11/03

DIMENSION SHEET FOR CAT. NO. M-8922
 REPAIRABLE NON-REPAIRABLE
B
M-8922
4