




REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	2019-09-13 01:00:00 EDT	DRAWING RELEASED	52158	JL	BE



ISOMETRIC VIEW

- NOTES:
1. DIMENSION IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
 2. APPROX. AMP. RATING: INDOOR 190, OUTDOOR 225, THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES:
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-361-6975 (QUEBEC)
 1-800-387-6487 (ALL OTHER PROVINCES)
 FOR PRODUCT INFO: <http://www.burndy.com>

BRAID	
ITEM NO:	27000728
CAT. NO:	BD15CG6
DRAWN BY:	R. BOISVERT 10/13/09
CHECKER:	J. PARKER 10/14/09
DSN APPVL:	J. PARKER 08/05/09
MFG APPVL:	L. LEAVITT 08/06/09
QA APPVL:	J. BRODEUR 08/10/09
MKT APPVL:	P. THERRIEN 08/05/09
PROD FAM:	MECHANICAL GROUNDING
PROJECT #:	--
DOCUMENT TYPE:	Sales
REL LEVEL:	RELEASED

SCALE:	1:1
DRAWING NO	CSC31721
REV	B
SHEET	1 OF 1

REV: PE0200

