


# Parkway SQUARE<sup>®</sup> *Sconce*



- ▶ Close-to-Wall Sconce
- ▶ New Configurable Styling
- ▶ LED Solutions Available



CodeLink<sup>SM</sup>



Spec Sheet

ARCHITECTURAL AREA LIGHTING

# Parkway Square – Sconce

## Newest Family Addition

Matches the style and shape of other Parkway Square models

## Configurable Design

Customize your design with unique decorative screens and finishes

## Advanced LED Technology

Bright, beautiful illumination with over 60,000 hours of life

## Two Housing Sizes

Choose medium or small housing solutions based on mounting height

## Easy Servicing

Contractor-friendly features make install and maintenance a breeze



## ORDERING INFORMATION

### 1. LUMINAIRE

#### Accent Scale (Small)

|           |                                |
|-----------|--------------------------------|
| PKSA DB   | Down beam & egress             |
| PKSA DS   | Down spread & egress           |
| PKSA UB   | Up beam & egress               |
| PKSA US   | Up spread & egress             |
| PKSA DBUS | Down beam/up spread & egress   |
| PKSA UBDS | Up beam/down spread & egress   |
| PKSA USDS | Up spread/down spread & egress |

#### Pedestrian Scale (Medium)

|           |                                |
|-----------|--------------------------------|
| PKSP DB   | Down beam & egress             |
| PKSP DS   | Down spread & egress           |
| PKSP UB   | Up beam & egress               |
| PKSP US   | Up spread & egress             |
| PKSP DBUS | Down beam/up spread & egress   |
| PKSP UBDS | Up beam/down spread & egress   |
| PKSP USDS | Up spread/down spread & egress |

### 2. BALLAST/DRIVER

#### PKSA

|          |   |
|----------|---|
| 15LED-WW | 15 LED array. Warm white (3500K). Class 2, 120 thru 277 volt. <b>DB/DS/UB/US only.</b>  |
| 15LED-BW | 15 LED array. Bright white (5100K). Class 2, 120 thru 277 volt. <b>DB/DS/UB/US only.</b>  |
| 24LED-WW | 24 LED array. Warm white (3500K). Class 2, 120 thru 277 volt. <b>DBUS/UBDS/USDS only.</b>   |
| 24LED-BW | 24 LED array. Bright white (5100K). Class 2, 120 thru 277 volt. <b>DBUS/UBDS/USDS only.</b>                                       |
| 24PLL    | 24 watt PL-L compact fluorescent electronic 120/277 volt ballast. <b>UB/DB only.</b>  |
| 35R111EB | 35 watt electronic metal halide R111, 120/277 volt. <b>UB/DB only.</b>  |
| 20MMC    | 20 watt electronic metal halide ballast, 120 thru 277 volt. Use PGJ5 base, MiniMastercolor lamp. <b>Not available with DB/UB.</b> |
| 39MMC    | 39 watt electronic metal halide ballast, 120 thru 277 volt. Use PGJ5 base, MiniMastercolor lamp. <b>Not available with DB/UB.</b> |
| DS20MMC  | Dual source 20 watt electronic metal halide ballast, 120 thru 277 volt. Use PGJ5 base, MiniMastercolor lamp. <b>USDS only.</b>    |
| DS39MMC  | Dual source 39 watt electronic metal halide ballast, 120 thru 277 volt. Use PGJ5 base, MiniMastercolor lamp. <b>USDS only.</b>    |

#### PKSP

|            |   |
|------------|---|
| 18LED-WW   | 18 LED array. Warm white (3500K). Class 2, 120 thru 277 volt. <b>DB/DS/UB/US only.</b>                                    |
| 18LED-BW   | 18 LED array. Bright white (5100K). Class 2, 120 thru 277 volt. <b>DB/DS/UB/US only.</b>                                  |
| 30LED-WW   | 30 LED array. Warm white (3500K). Class 2, 120 thru 277 volt. <b>DBUS/UBDS/USDS only.</b>                                 |
| 30LED-BW   | 30 LED array. Bright white (5100K). Class 2, 120 thru 277 volt. <b>DBUS/UBDS/USDS only.</b>                               |
| 55PLL      | 55 watt PL-L compact fluorescent electronic 120/277 volt ballast. <b>UB/DB only.</b>                                      |
| 70R111EB   | 70 watt electronic metal halide R111, 120/277 volt. <b>UB/DB only.</b>  |
| 35MHT6EB   | 35 watt electronic metal halide, 120 thru 277 volt ballast. Use G12 base, T-6 ceramic lamp.                               |
| 70MHT6EB   | 70 watt metal halide ballast, 120/277/347 volt ballast. Use G12 base, T-6 ceramic lamp.                                   |
| DS39MHT6EB | Dual source 39 watt electronic metal halide, 120 thru 277 volt ballast. Use G12 base, T-6 ceramic lamp. <b>USDS only.</b> |
| DS70MHT6EB | Dual source 70 watt electronic metal halide, 120 thru 277 volt ballast. Use G12 base, T-6 ceramic lamp. <b>USDS only.</b> |

Lamps not included, except LED. All applicable ballasts are EISA compliant.

### 3. DECORATIVE SCREENS (OPTIONAL)

|      |          |
|------|----------|
| DSIN | Infinity |
| DSOF | Offset   |
| DSWH | Wheat    |
| DSTR | Trio     |
| DSSH | Shutter  |
| DSCS | Custom*  |

\*Contact factory

### 4. OPTIONS

#### GENERAL

|     |  |
|-----|--|
| NEG | No egress lamp. Opening is sealed with a cap and painted to match fixture. |
| BBU | Integral battery backup. <b>24PLL for PKSA only.</b>                       |
| SSP | Screen in brushed stainless steel  |
| CPR | Screen in copper material  |

### 5. COLOR

All 13 standard and 4 premium AAL colors available. For custom colors, please submit a 4-digit RAL number.

## Ordering Information Example

|              |                   |                      |            |          |
|--------------|-------------------|----------------------|------------|----------|
| 1. LUMINAIRE | 2. BALLAST/DRIVER | 3. DECORATIVE SCREEN | 4. OPTIONS | 5. COLOR |
| PKSA DB      | 15LED-WW          | DSTR                 | NEG        | BLK      |

Refer to AAL's Parkway Square brochure for photometry and complete specification and ordering details.

