



# AIRO tradeSELECT®


Compact sleek design with high performance LED configurations and simple installation. The Airo Trade Select offers four stock configurations which include a universal mounting block for easy pole installation.



- Capable of replacing up to 250W-400W luminaires
- Featuring Micro Strike Optics which maximizes target zone illumination with minimal losses at the house-side, reducing light trespass issues
- Visual comfort standard
- Lens distributions are field rotatable (in 90deg increments)
- Backlight Controls and House Side Shields available
- 4000K CCT
- 1.5G rated for high vibration applications including bridges and overpasses



Universal Arm Mount (Standard)



Mast Arm Fitter (Accessory)




Wall Mount (Accessory)


## Performance Data

Stock Descriptions	Lumens	Wattage	HID Wattage Replacement	LED Count	CCT/CRI	Voltage	Distribution
ASL1-100-4W-ASQU	12,000	100W	250W	160L	4000K/70CRI	120-277V	4W
ASL1-100-3-ASQU	12,000	100W	250W	160L	4000K/70CRI	120-277V	3
ASL1-135-4W-ASQU	18,000	135W	400W	160L	4000K/70CRI	120-277V	4W
ASL1-135-3-ASQU	18,000	135W	400W	160L	4000K/70CRI	120-277V	3

### Type 3 Distribution




Airo: 135W at 25'




HID: 400W at 25'

### Type 4 Distribution



Airo: 135W at 25'



HID: 400W at 25'



**HUBBELL**  
Outdoor Lighting

Hubbell Outdoor Lighting • 701 Millennium Boulevard • Greenville, SC 29607  
www.hubbelloutdoor.com • 864-678-1000 - Rev. 11.16 • HOL0319



**HUBBELL**  
Lighting