



# MEDIMODE

Multi-Functional Recessed Patient Room Light



## PRODUCT OVERVIEW

MediMode is a multi-function lighting solution for the patient environment. Twin, indirect optical compartments deliver low-glare illumination for the patient while the center compartment can be activated to deliver an average of 100+ footcandles across the bed surface for critical examinations. An optional full lensed door is available to provide further sealing and to simplify cleaning.

## APPLICATIONS

- Patient Rooms
- Pre-and Post-Op Areas
- Emergency Room Examination
- Physician's Examination



## CANDELA PLOT

### Ambient-Reading

Report No.: 16.03364  
Model No.: MDM24-9-30-G-120-HLDA  
Lumens: 6263  
Input Watts: 95.1  
Efficacy: 65.9 Lm/W

### Examination (includes Ambient/Reading)

Report No.: 16.03363 + 16.03364  
Model No.: MDM24-9-30-G-120-HLDA  
Lumens: 14,191  
Input Watts: 189.1  
Efficacy: 75.0 Lm/W



0-deg - - - - -  
45-deg - - - - -  
90-deg - - - - -

0-deg - - - - -  
45-deg - - - - -  
90-deg - - - - -

## FUNCTIONS




Ambient-Reading



Examination

## DIMENSIONS

### Cross Section



Note: Dimensions shown are for MDM24 Grid model with HLDA door option. Refer to product specification sheet for the dimensions of other models.

### Top View

