

Canless Recessed Downlight



LITEBOX[®]

pro

LBRP

CANLESS RECESSED DOWNLIGHT




The LiteBox[®] Pro is a canless direct install downlighting family for New Construction or Remodel applications. Switchable lumen output, color temperature, and dial-in beam angle maximizes adjustability during installation.

FEATURES AND BENEFITS


- 4", 6" and 8" apertures, 800 to 5000 lumens
- Spun aluminum anodized or white trim, 55° cutoff
- Switchable Lumen, CCT, and Beam Angle
- Integral wiring compartment (standard)
- Optional support pans for Joist or T-Grid ceilings
- Universal 120-277V with 0-10V Dim to Off
- Long life L70 at >50,000 hrs (TM-21)
- Five year warranty



FIELD ADJUSTMENTS FOR EVERY APPLICATION




Easy integral switch allows a wide range of configurations.



Simply dial in desired beam on the jobsite. NO NEED TO CHANGE OUT OPTICS.

Reach new heights with higher lumen outputs and beam angle flexibility in one fixture.



2700K 3000K 3500K 4000K 5000K



9 Lumen Outputs in 3 Modules

FIXTURE MODULE

SL	ML	HL
800 1200 1600	1600 1800 2100	3000 4000 5000



9 Aperture/Finish Combinations

INTERCHANGEABLE TRIM

APERTURE	FINISH	
4"	6"	8"
DIFFUSE ANODIZED	WHITE CONE & FLANGE	DIFFUSE ANODIZED CONE & WHITE FLANGE

ORDERING GUIDE

EXAMPLE: LBRP-M-LSSLCS9 / LBRP-4RD-T-D

FIXTURE MODULE		TRIM		Notes	
Model/Type Configuration	Switchable Technology	Nominal Lumen Range	CCT/CRI		
LBRP-M	LS	SL 800/1200/1600 Lumens ML 1600/1800/2100 Lumens	CS9 Switchable CCT (2700/3000/3500/4000/5000K), 90 CRI		
LBRP-M Fixture Module, Round Direct Install, 120-277V with 0-10V Dim to Off	LS Switchable Lumen	HL 3000/4000/5000 Lumens ¹	27K9 2700K, 90 CRI 30K9 3000K, 90 CRI 35K9 3500K, 90 CRI 40K9 4000K, 90 CRI 50K9 5000K, 90 CRI		

Model	Aperture/Shape/Function	Trim	Reflector Finish/Color
LBRP	4RD 4" Round Downlight ¹ 6RD 6" Round Downlight 8RD 8" Round Downlight	T Trim	D Diffuse Clear Anodized WC White Cone and Flange DWT Diffuse Clear Anodized Cone & White Flange

¹ 4" Trim for use only with SL or ML Module.

Accessories

LB-4R-F-TG	Pan w/Bar Hangers for T-Grid/Joist, 4" Round
LB-4R-F-J	Pan Support for Joist, 4" Round
LB-6R-F-TG	Pan w/Bar Hangers for T-Grid/Joist, 6" Round
LB-6R-F-J	Pan Support for Joist, 6" Round
LB-8R-F-TG	Pan w/Bar Hangers for T-Grid/Joist, 8" Round
LB-8R-F-J	Pan Support for Joist, 8" Round



HUBBELL® Lighting

ARCHITECTURAL AREA LIGHTING

BEACON PRODUCTS

COLUMBIA LIGHTING

COMPASS

DUAL-LITE

HUBBELL CONTROL SOLUTIONS

HUBBELL OUTDOOR LIGHTING

KIM LIGHTING

KURT VERSEN

LITECONTROL

PRESCOLITE



701 Millennium Blvd. Greenville, SC 29607
Tel 864.678.1000
www.prescolite.com

03/17/22 PRE_LiteBox_Pro_sellsheet

Copyright © 2022 HLI Solutions, Inc. All rights reserved. Please refer to online specifications for most up-to-date content as specifications are subject to change without notice.