



## NEW! EMT INSULATING BUSHINGS



### Application

RACO® EMT insulating bushings provide a smooth surface for cable installation. Insulation prevents costly damage by protecting cable jacketing from sharp conduit edges during pulling.

Common applications include telephone, data, alarm/security, and other low voltage cable installations.

### Features

- High-density Polyethylene construction
- Temperature rated at 90° C
- Easy push-on design
- White color

### Complies with NEC Article 300.15c

| Catalog No. | Description                   | Unit Carton Qty. | Ship Carton Qty. | Ship Carton Weight (Lbs.) | Ship Carton 1 of 5 |
|-------------|-------------------------------|------------------|------------------|---------------------------|--------------------|
| 2172RAC     | 1/2" EMT Insulating Bushing   | 100              | 1000             | 17.13 x 9.5 x 9.75        | 50050169021724     |
| 2173RAC     | 3/4" EMT Insulating Bushing   | 100              | 1000             | 17.13 x 9.5 x 9.75        | 50050169021731     |
| 2174RAC     | 1" EMT Insulating Bushing     | —                | 100              | 6.75 x 6.25 x 7.75        | 50050169021748     |
| 2175RAC     | 1-1/4" EMT Insulating Bushing | —                | 100              | 6.75 x 6.25 x 7.75        | 50050169021755     |
| 2176RAC     | 1-1/2" EMT Insulating Bushing | —                | 100              | 6.75 x 6.25 x 7.75        | 50050169021762     |
| 2178RAC     | 2" EMT Insulating Bushing     | —                | 50               | 6.75 x 6.25 x 7.75        | 50050169021786     |
| 2180RAC*    | 2-1/2" EMT Insulating Bushing | —                | 25               | 8.25 x 8.25 x 8.5         | 50050169021809     |
| 2182RAC*    | 3" EMT Insulating Bushing     | —                | 25               | 8.25 x 8.25 x 8.5         | 50050169021823     |
| 2184RAC*    | 3-1/2" EMT Insulating Bushing | —                | 25               | 10.25 x 10.25 x 10.5      | 50050169021847     |
| 2186RAC*    | 4" EMT Insulating Bushing     | —                | 25               | 10.25 x 10.25 x 10.5      | 50050169021861     |

\*Can be used on Rigid/IMC Conduit