


HBLH SERIES



HBLH SERIES


HAZARDOUS LED HIGH BAY



- Class I, Division 2, Groups A, B, C & D
- Sealed optic for long life and UL1598 Wet Location Listing
- IP56
- Ideal for efficiently and economically lighting classified interior and industrial spaces
- Individually engineered LED optics providing optimally controlled and evenly distributed light
- Multiple LED configurations: 48, 60 and 72 LEDs on up to six individual light engines providing fail-safe redundancy
- Three distinct light distributions: aisle, narrow and wide
- High output LEDs deliver up to 100 lumens per watt
- 5 distinct color temperatures
- Specialized thermal management allows up to 45°C ambient temperature ratings
- Standard 0-10V Dimmable Drivers
- Minimum operating temperature of -40 °C
- Five Year Warranty

SPECIFICATIONS INFORMATION

ORDERING EXAMPLE: HBLH-72L-U-A-2-5K-N-070-WH



SERIES
HBLH Hazardous LED High Bay

NUMBER OF LEDs
48L 48 High Performance LEDs
60L 60 High Performance LEDs
72L 72 High Performance LEDs

VOLTAGE
U 120 - 277

MOUNT
A Pendant
C Cone
S Straight Stanchion
X Ceiling
Y Yoke

HUB
2 3/4"
 Available with A, C, X & Y Mounts
3 1"
 Available with A, C & X Mounts
4 1 1/4"
5 1 1/2"
 Available with S Mounts

COLOR TEMPERATURE
27K 2700° K
3K 3000° K
35K 3500° K
4K 4000° K
5K 5000° K

DISTRIBUTION
N Narrow
W Wide
A Aisle


DRIVE CURRENT
070 700MA

COLORS
TN Tan

OPTIONS
ENCA Acrylic Protective Lens
ENCG Glass Protective Lens
WG Zinc Plated Wire Guard


PHOTOMETRY

Aisle




HBLH-72LU-5K-A-070-WH

Narrow



HBLH-72LU-5K-N-070-WH

Wide



HBLH-72LU-5K-W-070-WH

