

**MINI**  
**LUNABAY**  
LED LOWBAY



**HUBBELL**  
Industrial Lighting

# MINI LUNABAY SERIES DECORATIVE LED LOW BAY



**HUBBELL**  
Industrial Lighting



- Ideal for retail and light industrial applications
- Up to 11,000 Lumens
- Reflector and Lens options available
- Suitable for operation in ambient temperatures ranging from -40°C to 35°C

## OPTICS



### WW22 TRANSLUCENT REFLECTOR:

- Translucent refractor
- Up to 90 lumens per watt
- Pleasant glow and low glare design with up light component (39%)
- Spacing to mounting height ratio of 1.7




### WA22 CLEAR ACRYLIC REFRACTOR:

- Clear Prismatic refractor 22" in Diameter
- 95 Lumens per watt
- Very Low Glare with strong up light component (29%)
- Batwing distribution for uniform lighting
- Spacing to mounting height ratio of 2.4



### SB22 TRANSLUCENT REFLECTOR:


- Translucent reflector
- Up to 95 LPW
- Pleasant glow and low glare
- Up light component of 33.9%
- Spacing to mounting height ratio of 2.0



### AL23 ALUMINUM REFRACTOR:


- Low glare bottom lens
- No up light
- Spacing to mounting height ratio of 2.1

## COLOR OPTIONS



**NOTE:**  
Printed color may vary from actual fixture color


## DIMENSIONS



LBS	A	B	C	D
	21"	10"	11"	16"

## PHOTOMETRY

PHOTOMETRIC REPORT: LBS-36DL-U-4K-A2-WA16-WH



### LUMINANCE DATA (cd sq.m)

ANGLE IN DEGREES	ANGLE 0-DEG
15	8471
25	7394
35	3900
45	985
55	408
65	259
75	151

### ZONAL LUMEN SUMMARY

ZONE	LUMENS
0-30	6656
0-40	9088
0-60	10307
0-90	10776

