



**CLH CLASSIFIED LOCATION HIGH BAY**



The CLH Series is ideal for hazardous location areas that demand a well-sealed high bay capable of replacing 400w MH high bays on a one-for-one basis. Its cast aluminum, well-sealed construction, smooth exterior and easy installation features make it an ideal choice for those tough locations in a facility.

- Three piece cast aluminum housing
- Easy one person installation on threaded conduit (¾" or 1")
- Four lens options
- Total input wattage of 220W, IP66
- Replacement for 400W PSMH
- Universal voltage of 120VAC - 277VAC/50/60 Hz
- Also available-347V & 480V
- Built to UL 1598 standard and certified by CSA
- Wet Location Listed, Class I, Division 2, Gas Groups A, B, C and D
- Five years warranty (Terms and Conditions apply)



## LENS OPTIONS



## APPLICATION



## EASE OF INSTALLATION



Slide top cover up onto conduit.  
Screw threaded knob on bottom of conduit.



Lift CLH in place on knob using keyhole in top of fixture.



Slide top cover down and screw to tighten (left hand thread).



**HUBBELL**  
Lighting

Due to our continued efforts to improve our products, specifications are subject to change without notice.  
© 2018 Hubbell Lighting. All Rights Reserved.

For more information visit our web site: <http://www.hubbellindustrial.com/>  
Phone: 1-864-678-1000