



\* Representative image

# Anchor, Lead, SS5, 10/12/14 X 7ft

by CHANCE Utility  
Catalog ID: 012642EJN

Square Shaft (SS 5) Lead Section, 7' (2134 mm) long with 10" (254 mm) - 12" (304 mm) - 14" (355 mm) Helices.

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

## Product Details

### General

Coating	Galvanized
Number of Helices	3
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb
Torque Rating	5500 ft-lbs
Type	Lead Sections
UPC	096359208297

### Dimensions

Anchor Helix Diameter(s)	10 in - 12 in - 14 in
Length	84.000 in
Weight	94.080 lb

### Certifications and Compliance

Industry Standard(s)	RUS Accepted
----------------------	--------------

### Logistics

Pallet Quantity	20 EA
Standard Package	1

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: hpscsc@hubbell.com

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: hpsintlcs@hubbell.com