



\* Representative image

# Anchor, Lead, Round Rod, 8/10 X 7ft

by CHANCE Utility  
Catalog ID: 012690AE

Round Rod Lead Section, 7' (2134 mm) long with 8" (203 mm) - 10" (254 mm) Helices.

- The Round-Rod "RR" multi-helix anchors are used in areas where weak soil conditions exist and moderate holding capacities are required
- Hot dipped galvanized per ASTM A153, Black asphalt paint applied over galvanizing, plastic tube assembled on rod
- RR screw anchors consist of three galvanized components: Lead section, extension shaft (which includes an integral coupling), and the guy adapter.

## Product Details

### General

Coating	Galvanized
Number of Helices	2
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb
Torque Rating	2300 ft-lbs
Type	Round Rod Anchors
UPC	096359208327

### Dimensions

Anchor Helix Diameter(s)	8 in - 10 in
Length	84.000 in
Weight	48.020 lb

### Logistics

Pallet Quantity	20 EA
Standard Package	1

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsh@hubbell.com](mailto:hpscsh@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)