



\* Representative image

## Anchor, PISA 4, 2-8in, 1in threads

by CHANCE Utility  
Catalog ID: 012904

Standard Strength Anchor Helix.- 4,000 Ft Lbs ( 5,424 N-M), two 8" (203 mm) Helices for use with 0.75" (19.1 mm) or 1" (25.4 mm) Rod.

- Installed with Chance anchor wrench C1021583
- Anchor has curvilinear leading edges to help penetrate rocky soils and to reduce damage during installation
- 1" threads to fit 3/4" and 1" diameter Pisa rod
- Anchors are painted with a black paint

## Product Details

### General

Coating	Painted
Number of Helices	2
Torque Rating	4000 ft-lbs
Type	Anchor Helix
UPC	096359208358

### Dimensions

Anchor Helix Diameter(s)	8 in - 8 in
Anchor Hub Size	1.375 in
Rod Diameter	<ul style="list-style-type: none"> <li>• 0.750</li> <li>• 1.000 in</li> </ul>
Weight	22.275 lb

### Logistics

Pallet Quantity	30 EA
Standard Package	1

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: hpscsc@hubbell.com

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: hpsintlcs@hubbell.com