




INSULATED BUSHINGS

Insulated Bushings Malleable Iron
N/A

B41



Catalog #: 1127

APPLICATIONS

For use on threaded rigid/IMC conduit to provide a smooth rounded surface at the entrance of raceways
N/A

PRODUCT FEATURES

Insuliner temperature rated at 150 degrees Celsius
Malleable iron construction insures mechanical protection for the raceway
Zinc electro plated for added corrosion protection
1/2 in. to 1 in. trade sizes are also available in die cast zinc

UL LISTED

Standard 514B, UL Listed E195969

CSA

C22.2 No. 18

GENERAL PRODUCT INFORMATION

Trade Size: 3 in.

DRAWING DIMENSIONS

Dimension A: 3-7/8 in.
Dimension B: 15/16 in.
Dimension C: 2-29/32 in.

PACKAGING

Package Type: Carton
Ship Carton Qty.: 5
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 44.40
Ship Carton Length (in.): 5.50
Ship Carton Width (in.): 4.50
Ship Carton Height (in.): 4.75
Ctn Weight (Lbs.): 2.22
UPC Number: 050169011270
I2of5: 50050169011275