


**SEALING LOCKNUTS****Sealing Locknuts Steel****B38**

Catalog #: 1203

APPLICATIONS

For use on threaded rigid/IMC conduit to provide a liquidtight seal against water and oil
 RACO sealing locknuts may be used with either sheet metal or cast enclosures

PRODUCT FEATURES

Fused-in-place gasket guarantees a liquidtight seal
 Use RACO sealing locknuts as an economical alternative to a threaded enclosure connector
 All steel construction insures mechanical protection
 Zinc electro plated for corrosion protection
 N/A

UL LISTED

Standard 514B (part numbers 1202-1210), UL File E195969

CSA

C22.2 No. 18 (part numbers 1202-1211)

COMPLIANCES

MSDS
www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_WP_Boxes_and_Fittings,January_2015.pdf

GENERAL PRODUCT INFORMATION

Trade Size: 3/4 in.

DRAWING DIMENSIONS

Dimension A: 1-25/64 in.
 Dimension B: 63/64 in.
 Thread Spec. C: 3/4 in. - 14 NPT
 Dimension D: 15/64 in.

PACKAGING

Package Type: Carton
 Ship Carton Qty.: 100
 Product UPC-A Labeled: No
 Weight (Lbs. Per/C): 2.90
 Ship Carton Length (in.): 6.25
 Ship Carton Width (in.): 4.50
 Ship Carton Height (in.): 4.25
 Ctn Weight (Lbs.): 2.90
 UPC Number: 050169012031
 I2of5: 50050169012036