


BONDING LOCKNUTS
Bonding Locknuts Steel
 N/A

B37


Catalog #: 1242

APPLICATIONS

 For use on threaded rigid/IMC conduit
 Use bonding locknuts when additional locking and grounding connections are required in applications where severe vibration is encountered

PRODUCT FEATURES

 All steel construction insures mechanical protection
 Zinc electro plated for corrosion protection
 N/A

UL LISTED

Standard 514B, UL Listed E195975

CSA

C22.2 No. 18

GENERAL PRODUCT INFORMATION

Trade Size: 1/2 in.

DRAWING DIMENSIONS

 Dimension A: 1.35 in.
 Dimension B: 1.04 in.
 Thread Spec. C: 1/2 in. - 14 NPT
 Dimension D: .20 in.
 Dimension E: 6-32 x 1/2 in.

PACKAGING

 Package Type: Carton
 Ship Carton Qty.: 50
 Product UPC-A Labeled: No
 Weight (Lbs. Per/C): 5.00
 Ship Carton Length (in.): 6.25
 Ship Carton Width (in.): 4.50
 Ship Carton Height (in.): 4.25
 Ctn Weight (Lbs.): 2.50
 UPC Number: 050169012420
 I2of5: 50050169012425