




## 4 IN. OCTAGON DRAWN BOXES WITH ARMORED CABLE / METAL CLAD / FLEX CLAMPS

4 in. Octagon Box, 1-1/2 in. Deep - Drawn with Armored Cable/Metal Clad/Flex Clamps  
TS Bracket, 1/2 in. Setback

A40



Catalog #: 155

### APPLICATIONS

RACO® Octagon Boxes are used in the installation of ceiling or wall lighting fixtures  
N/A

### PRODUCT FEATURES

RACO® offers a variety of labor saving mounting brackets that allow for easy positioning of box along studs or joists  
Reference the Box Selection section in the front of this catalog for complete description of bracket types and features  
Combination screw heads provide for faster installation

### UL LISTED

File E195978

### GENERAL PRODUCT INFORMATION

Wiring System: Armored Cable/Metal Clad/MCI-A/Flex

### RECOMMENDED MAX LOAD

Ceiling Fan (Dynamic) Lbs.: No  
Fixture (Static) Lbs.: 50

### CONFIGURATION

Cable Pairs: 4  
Bracket Type: TS, for Metal or Wood Studs  
Bracket Setback: 1/2 in.  
Drawn or Welded: Drawn  
Raised Ground: No  
Side Knockout(s): (1) 1/2 in.  
Bottom Knockouts(s): (1) 1/2 in.

### DRAWING DIMENSIONS

Dimension A: 1-1/2 in.  
Dimension B: 4 in.  
Dimension C: 7 in.  
Dimension D: 1/2 in.  
Dimension E: 1-1/16 in.

### PRODUCT MEASUREMENTS

Depth: 1-1/2 in.  
Cubic Inches (cm<sup>3</sup>): 15.5 (254.0)  
Wt. Ea. (Lbs.): 0.684  
Product Length (in.): 1.56  
Product Width (in.): 7.00  
Product Height (in.): 3.88

### PACKAGING

Minimum Pack Qty.: 50  
Std. Pkg.: 50  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 68.40  
Ship Carton Length (in.): 22.25  
Ship Carton Width (in.): 8.75  
Ship Carton Height (in.): 9.50  
Ctn Weight (Lbs.): 34.20  
Pallet Qty: 2250  
UPC Number: 050169001554  
I2of5: 50050169001559