


**RIGID SHORT ELBOWS - MALLEABLE IRON****90 Degree Short Elbow, Uninsulated Malleable Iron
N/A****B28**

Catalog #: 1722

APPLICATIONS

For use with threaded rigid/IMC conduit
 90 degree short elbows are ideal for use in tight locations where bending of conduit is not practical

PRODUCT FEATURES

All malleable iron construction insures mechanical protection for the raceway
 All components are zinc electro plated for corrosion protection
 N/A

UL LISTED

Standard 514B

GENERAL PRODUCT INFORMATION

Trade Size: 1/2 in.

DRAWING DIMENSIONS

Dimension A: 1-5/64 in.
 Dimension B: 3/4 in.
 Dimension C: 1-1/16 in.
 Dimension D: 1-17/32 in.
 Dimension E: 1/2 in.
 Dimension F: 39/64 in.
 Dimension G: 1/2 in. - 14 NPS

PACKAGING

Package Type: Carton
 Ship Carton Qty.: 50
 Product UPC-A Labeled: No
 Weight (Lbs. Per/C): 15.90
 Ship Carton Length (in.): 10.00
 Ship Carton Width (in.): 5.25
 Ship Carton Height (in.): 4.31
 Ctn Weight (Lbs.): 7.95
 UPC Number: 050169017227
 I2of5: 50050169017222