



Catalog # 189HS


# 4 IN. SQUARE BOX, WELDED, 1-1/2 IN. DEEP WITH EIGHT 1/2 IN. KO'S & FIVE TKO'S,

## RAISED GROUND, 10 IN. #12 SOLID COPPER PIGTAIL, UBS, HM BRACKET

Designed to enclose electrical wiring, switches, receptacles or lighting fixtures. Constructed from 1/16 In. pre-galvanized steel. 8-32 cover mounting screws assembled.

### FEATURES

- TKO knockout design provides installation flexibility
- UBS integrated support provides the bracing on back of box for wall cavities between 2-1/2 In - 6 In. thickness
- H/M style flush bracket
- Welded construction
- Eight 1/2 In. knockouts and five TKO knockouts
- 21.0 Cu. In. capacity
- Raised ground, 10 In. #12 Solid Copper pigtail
- Acceptable in 2-hour fire rated walls



### APPLICATIONS

Suitable for use without a bonding jumper in circuits up to 600V.

### CERTIFICATIONS



### SPECIFICATIONS

UPC NUMBER:	050169500378
EA LENGTH/DEPTH (IN.):	2.063
EA WIDTH (IN.):	4.913
EA HEIGHT (IN.):	4.000
WT. EA. (LBS.):	0.840
PACKAGE TYPE:	LOOSE
PRODUCT UPC-A LABELED:	NO

### PACKAGING

CASE I2OF5:	50050169500373
STANDARD CARTON QTY:	20
MIN ORDER QTY:	20



All RACO single-gang, two-gang, 4 in. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at [www.ul.com](http://www.ul.com)

**600V** Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

