



Catalog # 189M


4 IN. SQUARE BOX, WELDED, 1-1/2 IN. DEEP WITH SIX 1/2 IN. KO'S & FOUR TKO'S,

RAISED GROUND, 8 IN. #12 SOLID COPPER PIGTAIL, UBS, HM BRACKET

Designed to enclose electrical wiring, switches, receptacles or lighting fixtures.
Constructed from 1/16 In. pre-galvanized steel. 8-32 cover mounting screws assembled.

FEATURES

- TKO knockout design provides installation flexibility
- UBS integrated support provides the bracing on back of box for wall cavities between 2-1/2 In - 6 In. thickness
- H/M style flush bracket
- Welded construction
- Six 1/2 In. knockouts and four TKO knockouts
- 21.0 Cu. In. capacity
- Raised ground, 8 In. #12 Solid Copper pigtail
- Acceptable in 2-hour fire rated walls



APPLICATIONS

Suitable for use without a bonding jumper in circuits up to 600V.

CERTIFICATIONS



SPECIFICATIONS

UPC NUMBER:	050169500019
EA LENGTH/DEPTH (IN.):	2.063
EA WIDTH (IN.):	5.860
EA HEIGHT (IN.):	4.000
WT. EA. (LBS.):	0.870
PACKAGE TYPE:	LOOSE
PRODUCT UPC-A LABELED:	NO

PACKAGING

CASE 12OF5:	50050169500014
STANDARD CARTON QTY:	20
MIN ORDER QTY:	20



All RACO single-gang, two-gang, 4 in. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at www.ul.com

600V Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

