



**Commercial, Industrial
and Residential Electrical Products**

4 In. Square Box, Welded, 1-1/2 In. Deep with Ten 1/2 In. KO and Six TKO's

Catalog #:
189RAC



FEATURE BENEFIT

Shallow box features welded construction

PRODUCT FEATURES

- TKO knockout design provides installation flexibility
- Combination screw heads allow quick installation
- Welded construction
- Ten 1/2 in. knockouts and six TKO knockouts
- 21.0 cu. in. capacity
- Acceptable in 2-hour fire rated walls

APPLICATIONS

- Designed to enclose electrical wiring, switches, receptacles or lighting fixtures
- Constructed from 1/16 In. pre-galvanized steel
- 8-32 cover mounting screws assembled

CERTIFICATIONS



PRODUCT SPECIFICATIONS

| | |
|------------------------|--------------|
| UPC Number: | 050169501894 |
| Ea Length/Depth (in.): | 1.563 |
| Ea Width (in.): | 4.00 |
| Ea Height (in.): | 4.00 |
| Wt. Ea. (Lbs.): | 0.703 |
| Package Type: | Loose |
| Product UPC-A Labeled: | No |



PACKAGING

| | |
|----------------------|----------------|
| Case I2of5: | 50050169501899 |
| Standard Carton Qty: | 50 |
| Min Order Qty: | 50 |



All RACO single-gang, two-gang, 4 In. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at www.ul.com

600V

Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

Revision 1, November 2019



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

RACO
3902 W. Sample St.
South Bend, IN 46619
574-234-7151
www.hubbell.com/raco/en

