



# 0° Communication Standoff Bracket, 18"

by CHANCE Utility  
Catalog ID: 1CSM180

18" Medium Duty Fiberglass 0° Communication Standoff Bracket



\* Representative image

## Product Details

### General

|                                                      |                     |
|------------------------------------------------------|---------------------|
| Description - End Fitting                            | Communication clamp |
| Strength Rating - Minimum Ultimate, Longitudinal (L) | 700 lb              |
| Strength Rating - Minimum Ultimate, Transverse (T)   | 1,500 lb            |
| Strength Rating - Minimum Ultimate, Vertical (V)     | 1,500 lb            |
| UPC                                                  | 096359408222        |

### Dimensions

|                           |                   |
|---------------------------|-------------------|
| Diameter - Rod / Tube     | 1.5 in            |
| Distance From Pole        | 18.00 in          |
| Length                    | 18.00 in          |
| Mounting Bolt Spacing     | 6.00 in - 8.00 in |
| Radius - FWDE Wrap-Around | 1.5               |
| Weight                    | 4.6 lb            |

### Electrical Ratings

|       |         |
|-------|---------|
| Phase | 1-Phase |
|-------|---------|

### Logistics

|                  |        |
|------------------|--------|
| Pallet Quantity  | 216 EA |
| Standard Package | 1      |

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: hpscsc@hubbell.com

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: hpsintlcs@hubbell.com