



Vertical Pin Standoff Bracket, 24"

by CHANCE Utility
Catalog ID: 1SBH24V4

24" Heavy Duty Fiberglass Single-Phase Vertical Pin Standoff Bracket
with 1.375" Lead Threads



* Representative image

Product Details

General

Description - End Fitting	Vertical Pin
Material - Threads	1.375" Lead Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1850 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2100 lb
UPC	096359067368

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	24 in
Length	24.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 8.00 in• 10.00 in
Weight	12.7 lb

Logistics

Pallet Quantity	48 EA
Standard Package	2

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com