



**VAPOR BARRIER NON-METALLIC CABLE BOXES**

Vapor Barrier Cable Boxes  
2-3/4 in. Deep, 18.0 Cu. in., 1/2 in. Setback

A83



Catalog #: 2011-FBAR

**APPLICATIONS**

Vapor barrier boxes prevent unwanted penetration of exterior air and help maintain the existing interior environment from elements outside the structure  
RACO® nonmetallic vapor barrier cable boxes provide the installer with a cost alternative that is lightweight and east to install and provide excellent protection for wiring system or devices  
RACO® Nonmetallic cable boxes are used in branch circuit wiring to splice wires and accommodates wiring devices such as switches and receptacle

**PRODUCT FEATURES**

- Self-clamping wire entry clamps
- Vapor/air barrier flange and integral wire entry seal provides superior energy savings and quick installation
- Hands free installation for 1/2", 5/8", or 3/4" drywall
- N/A

**CSA**

CSA C22.2 #18

**GENERAL PRODUCT INFORMATION**

Wiring System:	Nonmetallic Sheathed Cable
Color:	Yellow

**RECOMMENDED MAX LOAD**

Ceiling Fan (Dynamic) Lbs.:	No
Fixture (Static) Lbs.:	50

**CONFIGURATION**

Cable Clamps:	4
Bracket Type:	Flush
Bracket Setback:	1/2 in.

**DRAWING DIMENSIONS**

Dimension A:	2-3/4 in.
--------------	-----------

**PRODUCT MEASUREMENTS**

Depth:	2-3/4 in.
Cubic Inches (cm3):	18.0 (295.0)
Wt. Ea. (Lbs.):	0.256
Product Length (in.):	3.13
Product Width (in.):	3.63
Product Height (in.):	4.63

**PACKAGING**

Minimum Pack Qty.:	50
Std. Pkg.:	50
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	25.60
Ship Carton Length (in.):	0.00
Ship Carton Width (in.):	0.00
Ship Carton Height (in.):	0.00
Ctn Weight (Lbs.):	0.00
Pallet Qty:	1200
UPC Number:	080503505189
I2of5:	30805035049915