




CONDUIT HANGERS

Conduit Hangers with Nut and Bolt, Steel
N/A

B84



Catalog #: 2041

APPLICATIONS

For use in wet or dry locations to support runs of rigid/IMC and EMT conduit from ceilings and walls
N/A

PRODUCT FEATURES

Furnished with a nut and bolt to speed installation
Pregalvanized finish provides corrosion protection

UL LISTED

Standard 514B (trade size 0-9)

CULUS

Canada (trade size 0-9)

GENERAL PRODUCT INFORMATION

Trade Size: 2-1/2
EMT Size: 1-1/4 in.
Max Load Lbs.: 75

DRAWING DIMENSIONS

Dimension A: 1.50 in.
Dimension B: .87 in.
Dimension C: .04 in.
Dimension D: .25 in.

PACKAGING

Package Type: Carton
Ship Carton Qty.: 100
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 13.20
Ship Carton Length (in.): 10.60
Ship Carton Width (in.): 12.50
Ship Carton Height (in.): 8.50
Ctn Weight (Lbs.): 13.20
UPC Number: 050169020418
I2of5: 50050169020413