




CONDUIT HANGERS

Conduit Hangers with Nut and Bolt, Steel
N/A

B84



Catalog #: 2055

APPLICATIONS

For use in wet or dry locations to support runs of rigid/IMC and EMT conduit from ceilings and walls
N/A

PRODUCT FEATURES

Furnished with a nut and bolt to speed installation
Pregalvanized finish provides corrosion protection

UL LISTED

Standard 514B (trade size 0-9)

CULUS

Canada (trade size 0-9)

GENERAL PRODUCT INFORMATION

Trade Size:	3
Rigid/IMC Size:	1-1/4 in.
EMT Size:	1-1/2 in.
Max Load Lbs.:	80

DRAWING DIMENSIONS

Dimension A:	1.70 in.
Dimension B:	.87 in.
Dimension C:	.04 in.
Dimension D:	.25 in.

PACKAGING

Package Type:	Carton
Ship Carton Qty.:	100
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	14.00
Ship Carton Length (in.):	10.60
Ship Carton Width (in.):	12.50
Ship Carton Height (in.):	8.50
Ctn Weight (Lbs.):	14.00
UPC Number:	050169020555
I2of5:	50050169020550