



**CONDUIT HANGERS****Conduit Hangers with Threaded Hole, Steel**
N/A**B84**

Catalog #: 2056TH

APPLICATIONSFor use in wet or dry locations to support runs of rigid/IMC and EMT conduit from ceilings and walls
N/A**PRODUCT FEATURES**Hangers are supplied with a retained bolt and threaded hole eliminating the need for a nut
The design allows for quick and easy installation using a screwdriver or nut driver
Pregalvanized finish provides corrosion protection**CULUS**

UL Listed E195968

GENERAL PRODUCT INFORMATIONTrade Size: 4
Rigid/IMC Size: 1-1/2 in.
Max Load Lbs.: 80**DRAWING DIMENSIONS**Dimension A: 1.92 in.
Dimension B: 1.00 in.
Dimension C: .055 - .062 in.
Dimension D: .33 in.**PACKAGING**Package Type: Carton
Ship Carton Qty.: 100
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 15.10
Ship Carton Length (in.): 13.60
Ship Carton Width (in.): 9.70
Ship Carton Height (in.): 6.70
Ctn Weight (Lbs.): 15.50
UPC Number: 050169911952
I2of5: 50050169911957