





CONDUIT HANGERS

Conduit Hangers with Threaded Hole, Steel
N/A

B84



Catalog #: 2058TH

APPLICATIONS

For use in wet or dry locations to support runs of rigid/IMC and EMT conduit from ceilings and walls
N/A

PRODUCT FEATURES

Hangers are supplied with a retained bolt and threaded hole eliminating the need for a nut
The design allows for quick and easy installation using a screwdriver or nut driver
Pregalvanized finish provides corrosion protection

CULUS

UL Listed E195968

GENERAL PRODUCT INFORMATION

| | |
|-----------------|-------|
| Trade Size: | 5 |
| Rigid/IMC Size: | 2 in. |
| EMT Size: | 2 in. |
| Max Load Lbs.: | 100 |

DRAWING DIMENSIONS

| | |
|--------------|-----------------|
| Dimension A: | 2.30 in. |
| Dimension B: | 1.00 in. |
| Dimension C: | .055 - .062 in. |
| Dimension D: | .33 in. |

PACKAGING

| | |
|---------------------------|----------------|
| Package Type: | Carton |
| Ship Carton Qty.: | 50 |
| Product UPC-A Labeled: | No |
| Weight (Lbs. Per/C): | 16.90 |
| Ship Carton Length (in.): | 10.40 |
| Ship Carton Width (in.): | 10.40 |
| Ship Carton Height (in.): | 4.80 |
| Ctn Weight (Lbs.): | 8.85 |
| UPC Number: | 050169911969 |
| I2of5: | 50050169911964 |