


**FLEXIBLE METAL STRAIGHT SQUEEZE CONNECTORS**Straight Squeeze Connectors, Uninsulated Malleable Iron  
N/A**B61**

Catalog #: 2102-8

**APPLICATIONS**For use in dry locations to bond flexible metal conduit to a box or enclosure  
N/A**PRODUCT FEATURES**All malleable iron construction insures mechanical protection for the raceway  
Electro zinc plated for added corrosion protection  
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation**CULUS**

UL Listed E195969

**GENERAL PRODUCT INFORMATION**

Trade Size: 1/2 in.

**DRAWING DIMENSIONS**Dimension A: 1-33/64 in.  
Dimension B: 17/32 in.  
Thread Spec. B: 1/2 in. - 14 NPS  
Dimension C: .590 in.  
Dimension D: .855 - .910  
Dimension E: 1-5/8 in.**PACKAGING**Package Type: Carton  
Std. Pkg.: 1  
Ship Carton Qty.: 25  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 14.40  
Ship Carton Length (in.): 8.75  
Ship Carton Width (in.): 5.00  
Ship Carton Height (in.): 4.00  
Ctn Weight (Lbs.): 3.60  
UPC Number: 050169210284  
I2of5: 50050169210289