



**Commercial, Industrial  
and Residential Electrical Products**

## 4 In. Square Box, Welded, 1-1/2 In. Deep with NMSC Clamps, Five 1/2 In. KO's and Two TKO's

Catalog #:  
211



### FEATURE BENEFIT

Shallow 1-1/2 In. deep steel box features built in clamps for {NMSC} nonmetallic sheathed cable

### PRODUCT FEATURES

- Welded steel construction with clamps for {NMSC} nonmetallic sheathed cable clamps
- 4 In. square x 1-1/2 In. deep
- TKO® Knockouts allow for design and installation flexibility
- Supplied with five 1/2 In. and two 1/2-3/4 In. TKO® knockouts
- Combination Phillips/slotted screw heads
- 21.0 cu. In. capacity
- Acceptable for use in 2-hour fire rated walls

### APPLICATIONS

- RACO® Boxes are installed in walls or ceilings for lighting fixtures, switches or receptacles
- Square boxes are used where multiple conductors runs are split into two or more directions to bring power to a number of electrical devices

### CERTIFICATION



### PRODUCT SPECIFICATIONS

UPC Number:	050169902110
Ea Length/Depth (in.):	1.563
Ea Width (in.):	4.00
Ea Height (in.):	4.00
Wt. Ea. (Lbs.):	0.771
Package Type:	Loose
Product UPC-A Labeled:	No

### PACKAGING

PK 12of5:	50050169902115
Standard Carton Qty:	50
Min Order Qty:	50



All RACO single-gang, two-gang, 4 In. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at [www.ul.com](http://www.ul.com)

Revision 1, November 2019



**RACO**  
3902 W. Sample St.  
South Bend, IN 46619  
574-234-7151  
[www.hubbell.com/raco/en](http://www.hubbell.com/raco/en)

