


**FLEXIBLE METAL STRAIGHT SQUEEZE CONNECTORS**Straight Squeeze Connectors, Uninsulated Malleable Iron  
N/A**B61**

Catalog #: 2110

**APPLICATIONS**For use in dry locations to bond flexible metal conduit to a box or enclosure  
N/A**PRODUCT FEATURES**All malleable iron construction insures mechanical protection for the raceway  
Electro zinc plated for added corrosion protection  
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation**CULUS**

UL Listed E195969

**GENERAL PRODUCT INFORMATION**

Trade Size: 2-1/2 in.

**DRAWING DIMENSIONS**

Dimension A:	3 in.
Dimension B:	1-3/64 in.
Thread Spec. B:	2-1/2 in. - 8 NPS
Dimension C:	2.358 in.
Dimension D:	3.080 MAX
Dimension E:	4-5/32 in.

**PACKAGING**

Package Type:	Carton
Ship Carton Qty.:	1
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	171.90
Ship Carton Length (in.):	10.90
Ship Carton Width (in.):	7.80
Ship Carton Height (in.):	3.50
Ctn Weight (Lbs.):	8.60
UPC Number:	050169021101
I2of5:	50050169021106