#### BEI R CO C HUBBELL Δ 4

# Insulated Set Screw Connector, Steel

B03



Catalog #: 2124US

#### APPLICATIONS

For use in dry locations to bond EMT conduit to a box or enclosure. RACO steel set screw connectors provide concrete-tight connections when taped.

#### PRODUCT FEATURES

All steel construction insures mechanical protection for the raceway Tri-head screws may be installed using a slotted, Phillips, or Robertson head screwdriver

2-1/2 in. to 4 in. trade sizes are also UL listed for use on Rigid/IMC conduit, allowing for design and installation flexibility All components are zinc electroplated for corrosion protection 1/2 in. to 1 in. trade sizes have one set screw, 1-1/4 in. to 4 in. trade sizes have two set screws UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation

#### UL LISTED

2-1/2" - 4" Standard 514B, File E195969, E195970

### CULUS

1/2" - 2" Standard 514B, C22.2 # 18

Ship Carton Width (in.): Ship Carton Height (in.): Pallet Qty:

UPC Number:

## COMPLIANCES

MSDS www.hubbell-rtb.com/certifications/Hubbell-RACO\_MSDS\_for\_WP\_Boxes\_and\_Fittings,January 2015.pdf

GENERAL PRODUCT INFORMATION Sub Class:	Insulated
Trade Size:	1 in.
DRAWING DIMENSIONS	
Dimension A:	1.81 in.
Dimension B:	1.194 in.
Dimension D:	.391 in.
Dimension E:	#12-28UNF
PACKAGING	
Package Type:	Carton
Std. Pkg.:	20
Ship Carton Qty .:	100
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	23.00
Ship Carton Length (in.):	10.00

10.00 5.25 4.31 6400 050169570142