



* Representative image

15 kV Class Elbow Arrester (12.7 kV MCOV)

by Hubbell Power Systems
Catalog ID: 215ELA15

Deadfront Elbow Arrester, 15kV 12.7 MCOV

Product Details

General

Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359360490

Dimensions

Height	10.200 in
Maximum Operating Altitude	6000 ft
Weight	5.200 lb

Electrical Ratings

Duty Cycle	15 kV
MCOV	12.7 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> • 45.5 kV @ 1.5 kA • 48.5 kV @ 3 kA • 52 kV @ 5 kA • 57.5 kV @ 10 kA • 67.5 kV @ 20 kA • 87.5 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	40.0 kV
kV Class	15 kV

Logistics

Pallet Quantity	108 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com