



* Representative image

15kV Fused Elbow, 0.610 - 0.823 Cable insulation dia range, Hi-Tech® Fuse Connector

by Hubbell Power Systems
Catalog ID: 215FEHA3

Fused Elbow, 15 kV, with Test Point, Cable Insulation Diameter range = 0.610 - 0.823 inches, #1 Solid or Compact and #2 Stranded or Compressed, Accepts Hi-Tech® EFX Current Limiting Fuses

Product Details

General

Connector Type	Hi-Tech® Fuse Connector
Integral Seal	No
PROBELOK® Connectors	No
Type	200A Loadbreak
UPC	096359669432
With Seal Kit	No
With Test Point	Yes

Dimensions

Cable Insulation Diameter Maximum	0.823 in
Cable Insulation Diameter Minimum	0.610 in
Weight	7.0 lb

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

Conductor Related

Cable Insulation Diameter Range	0.610 - 0.823
Solid or Compacted Conductor	#1
Stranded or Compressed Conductor	#2

Logistics

Pallet Quantity	240 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com