



* Representative image

15 kV, Load Break Elbow w/ Bimetal Contact

by Hubbell Power Systems
Catalog ID: 215LE43

Load Break Elbow, 200 Amp, 15 kV, Long Bimetal Contact, Cable Insulation Diameter range = 0.635 - 0.905 inches, #1 Solid or Compacted and #2 Stranded or Compressed

Product Details

General

Connector Type	Bi-Metal
Integral Seal	No
PROBELOK® Connectors	No
Type	200Amp Load Break
UPC	096359498360
With Seal Kit	No
With Test Point	No

Dimensions

Cable Insulation Diameter Maximum	0.905 in
Cable Insulation Diameter Minimum	0.635 in
Weight	2.750 lb

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

Conductor Related

Cable Insulation Diameter Range	0.635 - 0.905
Solid or Compacted Conductor	#1
Stranded or Compressed Conductor	#2

Logistics

Pallet Quantity	240 EA
Standard Package	20

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com