



\* Representative image

# 15 kV, Load Break Elbow w/ Bimetal Contact

by Hubbell Power Systems  
Catalog ID: 215LE45

Load Break Elbow, 200 Amp, 15 kV, Long Bimetal Contact, Cable Insulation Diameter range = 0.635 - 0.905 inches, 2/0 Solid or Compacted and 1/0 Stranded or Compressed

## Product Details

### General

Connector Type	Bi-Metal
Integral Seal	No
PROBELOK <sup>®</sup> Connectors	No
Type	200Amp Load Break
UPC	096359498377
With Seal Kit	No
With Test Point	No

### Dimensions

Cable Insulation Diameter Maximum	0.905 in
Cable Insulation Diameter Minimum	0.635 in
Weight	2.750 lb

### Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

### Conductor Related

Cable Insulation Diameter Range	0.635 - 0.905
Solid or Compacted Conductor	2/0
Stranded or Compressed Conductor	1/0

### Logistics

Pallet Quantity	240 EA
Standard Package	20

For further technical assistance, please contact us

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscshubbell.com](mailto:hpscshubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)