



15 kV, Load Break Elbow w/ Bimetal Contact, Seal Kit

by Hubbell Power Systems
Catalog ID: 215LE57J

Load Break Elbow, 200 Amp, 15 kV, Long Bimetal Contact, Cable Insulation Diameter range = 0.760 - 1.135 inches, 4/0 Solid or Compacted and 3/0 Stranded or Compressed, Seal Kit



* Representative image

Product Details

General

Connector Type	Bi-Metal
Integral Seal	No
PROBELOK [®] Connectors	No
Type	200Amp Load Break
UPC	096359573685
With Seal Kit	Yes
With Test Point	No

Dimensions

Cable Insulation Diameter Maximum	1.135 in
Cable Insulation Diameter Minimum	0.760 in
Weight	3.250 lb

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

Conductor Related

Cable Insulation Diameter Range	0.760 - 1.135
Solid or Compacted Conductor	4/0
Stranded or Compressed Conductor	3/0

Logistics

Pallet Quantity	120 EA
Standard Package	20

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com