




EMT SET SCREW CONNECTORS

Insulated Set Screw Connector, Steel

B03



Catalog #: 2166

APPLICATIONS

For use in dry locations to bond EMT conduit to a box or enclosure. RACO steel set screw connectors provide concrete-tight connections when taped.
For use in dry locations to bond unthreaded rigid/IMC conduit to a box or enclosure. RACO steel set screw connectors provide concrete-tight connections when taped.

PRODUCT FEATURES

- All steel construction ensures mechanical protection for the raceway
- Tri-head screws may be installed using a slotted, Phillips, or Robertson head screwdriver
- 2-1/2 in. to 4 in. trade sizes are also UL listed for use on EMT or Rigid/IMC conduit, allowing for design and installation flexibility
- All components are zinc electroplated for corrosion protection
- 1/2 in. to 1 in. trade sizes have one set screw, 1-1/4 in. to 4 in. trade sizes have two set screws
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation

UL LISTED

2-1/2" - 4" Standard 514B, File E195969, E195970
Standard 514B, UL Listed E195969

CULUS

1/2" - 2" Standard 514B, C22.2 # 18

COMPLIANCES

MSDS
www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_WP_Boxes_and_Fittings.January_2015.pdf

GENERAL PRODUCT INFORMATION

Sub Class: Insulated
Trade Size: 4 in.

DRAWING DIMENSIONS

Dimension A:	3.54"
Dimension B:	4.56"
Dimension D:	.717"
Dimension E:	1/4 - 28

PACKAGING

Package Type:	Carton
Ship Carton Qty.:	1
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	243.8
Ship Carton Length (in.):	5.50
Ship Carton Width (in.):	5.50
Ship Carton Height (in.):	4.19
Ctn Weight (Lbs.):	2.44
Pallet Qty:	448
UPC Number:	050169021668