



\* Representative image

## Under-Oil Arrester (15.3 kV MCOV, 3001 Hardware)

by OHIO BRASS  
Catalog ID: 2211153001

IEEE Heavy Duty / IEC Distribution High Under-Oil Surge Arrester

- HPS under-oil arresters comply with the latest revision of the IEEE C62.11, as well as IEC 60099-4
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina
- 100% routine tested

### Product Details

#### General

Application	Under Oil
Mounting Hardware	Bracket
Mounting Type	Bracket
UPC	096359417057

#### Dimensions

Length	8.76 in
--------	---------

#### Electrical Ratings

BIL	125 kV
Current Rating	500 A
Duty Cycle	18 kV
Frequency Rating	48-62 Hz
MCOV	15.3 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	54.72
Maximum Discharge Voltage	<ul style="list-style-type: none"> <li>• 50.49 kV @ 1.5 kA</li> <li>• 53.17 kV @ 3 kA</li> <li>• 55.62 kV @ 5 kA</li> <li>• 59.68 kV @ 10 kA</li> <li>• 66.06 kV @ 20 kA</li> </ul>
Maximum Switching Surge Protective Level @ 500A	47.09

#### Logistics

Pallet Quantity	120 EA
-----------------	--------

For further technical assistance, please contact us

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)