



* Representative image

Under-Oil Arrester (24 kV MCOV, 3001 Hardware)

by OHIO BRASS
Catalog ID: 2211243001

IEEE Heavy Duty / IEC Distribution High Under-Oil Surge Arrester

- HPS under-oil arresters comply with the latest revision of the IEEE C62.11, as well as IEC 60099-4
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina
- 100% routine tested

Product Details

General

Application	Under Oil
Mounting Hardware	Bracket
Mounting Type	Bracket
UPC	096359417101

Dimensions

Length	12.86 in
--------	----------

Electrical Ratings

BIL	150 kV
Current Rating	500 A
Duty Cycle	30 kV
Frequency Rating	48-62 Hz
MCOV	24 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	91.4
Maximum Discharge Voltage	<ul style="list-style-type: none"> • 80.52 kV @ 1.5 kA • 84.8 kV @ 3 kA • 88.7 kV @ 5 kA • 95.17 kV @ 10 kA • 105.36 kV @ 20 kA
Maximum Switching Surge Protective Level @ 500A	75.09

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com