



\* Representative image

# 25 kV Class Elbow Arrester (10.2 kV MCOV)

by Hubbell Power Systems  
Catalog ID: 225ELA12

Deadfront Elbow Arrester, 25kV 10.2 MCOV

## Product Details

### General

Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359392880

### Dimensions

Height	6.600 in
Maximum Operating Altitude	6000 ft
Weight	3.700 lb

### Electrical Ratings

Duty Cycle	12 kV
MCOV	10.2 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> <li>• 39 kV @ 1.5 kA</li> <li>• 41 kV @ 3 kA</li> <li>• 44 kV @ 5 kA</li> <li>• 49 kV @ 10 kA</li> <li>• 57 kV @ 20 kA</li> <li>• 74 kV @ 40 kA</li> </ul>
Maximum Switching Surge Protective Level @ 500A	34.0 kV
kV Class	25 kV

### Logistics

Pallet Quantity	108 EA
Standard Package	1

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)