



\* Representative image

# 25 kV Class Elbow Arrester (15.3 kV MCOV)

by Hubbell Power Systems  
Catalog ID: 225ELA18

Deadfront Elbow Arrester, 25kV 15.3 MCOV

## Product Details

### General

Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359266648

### Dimensions

Height	10.200 in
Maximum Operating Altitude	6000 ft
Weight	5.200 lb

### Electrical Ratings

Duty Cycle	18 kV
MCOV	15.3 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> <li>• 52 kV @ 1.5 kA</li> <li>• 56 kV @ 3 kA</li> <li>• 60 kV @ 5 kA</li> <li>• 66 kV @ 10 kA</li> <li>• 78 kV @ 20 kA</li> <li>• 101 kV @ 40 kA</li> </ul>
Maximum Switching Surge Protective Level @ 500A	46.0 kV
kV Class	25 kV

### Logistics

Pallet Quantity	108 EA
Standard Package	1

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: hpscsc@hubbell.com

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: hpsintlcs@hubbell.com