



* Representative image

25/28 kV, Load Break Elbow w/ Integral Seal, Test Point, Bimetal Contact

by Hubbell Power Systems
Catalog ID: 228LEJ45T

Load Break Elbow with Integral Seal, 200 Amp, 25/28 kV, with Test Point, Long Bimetal Contact, Cable Insulation Diameter range = 0.800 - 1.140 inches, 2/0 Solid or Compacted and 1/0 Stranded or Compressed

Product Details

General

Connector Type	Bi-Metal
Integral Seal	Yes
PROBELOK [®] Connectors	No
Type	200Amp Load Break
UPC	096359590880
With Seal Kit	No
With Test Point	Yes

Dimensions

Cable Insulation Diameter Maximum	1.140 in
Cable Insulation Diameter Minimum	0.800 in
Weight	3.000 lb

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	200 A
kV Class	25/28 kV

Conductor Related

Cable Insulation Diameter Range	0.800 - 1.140
Solid or Compacted Conductor	2/0
Stranded or Compressed Conductor	1/0

Logistics

Pallet Quantity	240 EA
Standard Package	20

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com