



**Commercial, Industrial
and Residential Electrical Products**

4 In. Square Box, Welded with STAB-IT® Connector, 2-1/8 In. Deep, Raised Ground, 8 In. #12 Solid Copper Pigtail, Cable Management Clip

Catalog #:
232SCM



FEATURE BENEFIT

Install MC cable 3x faster with our Stab-It connector. Holds 3 cables, removable. Saves time and money

PRODUCT FEATURES

- Welded steel construction with STAB-IT® connector and cable management clip
- 4 In. square x 2-1/8 In. deep
- TKO® Knockouts allow for design and installation flexibility
- Supplied with seven 1/2 In. and four 1/2-3/4 In. TKO® knockouts
- Combination Phillips/slotted screw heads
- 30.3 Cu. In. capacity
- Includes 8 In. #12 solid copper ground pigtail
- Acceptable for use in 2-hour fire rated walls

APPLICATIONS

Designed to enclose electrical wiring, switches, receptacles or lighting fixtures. Constructed from 1/16 In. pre-galvanized steel. 8-32 cover mounting screws assembled.

CERTIFICATIONS



PRODUCT SPECIFICATIONS

UPC Number:	050169892329
Ea Length/Depth (in.):	2.20
Ea Width (in.):	4.00
Ea Height (in.):	4.00
Wt. Ea. (Lbs.):	1.052
Package Type:	Loose
Product UPC-A Labeled:	No



All RACO single-gang, two-gang, 4 In. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at www.ul.com

SHIPPING

Case 12of5:	50050169892324
Standard Carton Qty:	25
Min Order Qty:	25

600V

Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

Revision 1, January 2020



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

RACO
3902 W. Sample St.
South Bend, IN 46619
574-234-7151
www.hubbell.com/raco/en

