




CONDUIT CLAMPS

Right Angle Clamp Galvanized Malleable Iron
N/A

B85



Catalog #: 2356RC

APPLICATIONS

To secure Rigid/IMC or EMT conduit across, parallel, or perpendicular to channel, beam, and angle supports
N/A

PRODUCT FEATURES

- Three styles meet every installation need
- Heavy duty U-bolts, hex bolts and hex nuts
- Capable of supporting heavy loads
- Hot dipped galvanized malleable iron construction provides excellent weatherability and corrosion protection
- Perfect for commercial construction applications

CULUS

UL Listed E195968

GENERAL PRODUCT INFORMATION

Trade Size: 1-1/2 in.

DRAWING DIMENSIONS

Dimension A: 2 in.
 Dimension B: 2-3/8 in.
 Dimension C: 3-1/2 in.
 Dimension D: 1-13/16 in.
 Dimension E: 3-1/4 in.

PACKAGING

Package Type: Carton
 Ship Carton Qty.: 25
 Product UPC-A Labeled: No
 Weight (Lbs. Per/C): 54.80
 Ship Carton Length (in.): 10.00
 Ship Carton Width (in.): 10.00
 Ship Carton Height (in.): 5.00
 Ctn Weight (Lbs.): 13.70
 UPC Number: 050169986240
 I2of5: 50050169986245