



* Representative image

35 kV Class Small Interface Elbow Arrester (22 kV MCOV)

by Hubbell Power Systems
Catalog ID: 235ELA27

Elbow Arrester, 35KV 22 MCOV, Mates with IEEE Std. 386, Interface 7B

Product Details

General

Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359266679

Dimensions

Height	13.700 in
Maximum Operating Altitude	6000 ft
Weight	6.500 lb

Electrical Ratings

Duty Cycle	27 kV
MCOV	22 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> • 78 kV @ 1.5 kA • 84 kV @ 3 kA • 90 kV @ 5 kA • 99 kV @ 10 kA • 117 kV @ 20 kA • 151.5 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	69.0 kV
kV Class	35 kV

Logistics

Pallet Quantity	64 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com