



\* Representative image

# 35 kV Class Small Interface Elbow Arrester (24.4 kV MCOV)

by Hubbell Power Systems  
Catalog ID: 235ELA30

Elbow Arrester, 35KV 24 MCOV, Mates with IEEE Std. 386, Interface 7B

## Product Details

### General

Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359433439

### Dimensions

Height	13.700 in
Maximum Operating Altitude	6000 ft
Weight	6.500 lb

### Electrical Ratings

Duty Cycle	30 kV
MCOV	24.4 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> <li>• 81 kV @ 1.5 kA</li> <li>• 88.5 kV @ 3 kA</li> <li>• 94.5 kV @ 5 kA</li> <li>• 108 kV @ 10 kA</li> <li>• 131.5 kV @ 20 kA</li> <li>• 159 kV @ 40 kA</li> </ul>
Maximum Switching Surge Protective Level @ 500A	74.0 kV
kV Class	35 kV

### Logistics

Pallet Quantity	64 EA
Standard Package	1

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: hpscsc@hubbell.com

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: hpsintlcs@hubbell.com